IEC Appliance Inlet C14 with Filter, Fuseholder 1- or 2-pole (5x20 mm or 6.3x32 mm), optional Voltage Selector (step switch)







KFC without voltage selector



Description

- Panel mount :

Screw-on mounting front side

- 4 Functions:

Appliance Inlet Protection class I , Fuseholder with interchangeable fuse drawer for Fuse-links $5x20\ mm$ or $6.3x32\ mm$, with or without voltage selector (step switch) , Line filter in standard and medical version

- Quick connect terminals 4.8 x 0.8 mm

Unique Selling Proposition

- Multifunctional power entry module
- Suitable for various fuses
- Highly resistant since fully potted
- V-Lock cord retaining

See below:

Approvals and Compliances

Characteristics

- All single elements are already wired
- The fuse drawer "Fingergrip" can be removed by hand
- For applications according IEC/UL 62368-1 we recommend variants with bleed resistor

Suitable for use in medical equipment according to IEC/UL 60601-1 (1 MOOP, 1 MOPP)

Other versions on request

- Variant with notch for V-Lock mating Cordsets

References

Alternative: version without line filter KEC Alternative: Standard version

Weblinks

pdf data sheet, html datasheet, General Product Information, Approvals, Distributor-Stock-Check, Accessories, Detailed request for product

Newly available variants corresponding to V-Lock mating cordset. The connector is equipped with a notch intended for use with the latching cordset. The cord latching system prevents against accidental removal of the cordset.

Technical Data

Ratings UL/CSA 1 - 10 A @ Ta 40 °C / 250 VAC; 60 Hz Leakage Current standard < 0.5 mA (250 V / 60 Hz) medical < 5 μA (250 V / 60 Hz)	Ratings IEC	1 - 10 A @ Ta 40 °C / 250 VAC; 50 Hz
medical < 5 μA (250 V / 60 Hz)Dielectric Strength> 1.7 kVDC between L-N	Ratings UL/CSA	1 - 10 A @ Ta 40 °C / 250 VAC; 60 Hz
	Leakage Current	,
Test voltage (2 sec)	Dielectric Strength	> 2.7 kVDC between L/N-PE
Allowable Operation Tempe25 °C to 85 °C rature		-25 °C to 85 °C
Climatic Category 25/085/21 acc. to IEC 60068-1	Climatic Category	25/085/21 acc. to IEC 60068-1
IP-Protection front side IP40 acc. to IEC 60529	IP-Protection	front side IP40 acc. to IEC 60529
Protection Class Suitable for appliances with protection class I acc. to IEC 61140	Protection Class	
Terminal Quick connect terminals 4.8 x 0.8 mm	Terminal	Quick connect terminals 4.8 x 0.8 mm
Panel Thickness S Screw: max 8 mm Mounting screw torque max 0.5 Nm	Panel Thickness S	001011111111111111111111111111111111111
Material Thermoplastic, black, UL 94V-0	Material	Thermoplastic, black, UL 94V-0

Appliance inlet/-outlet	C14 acc. to IEC 60320-1, UL 498, CSA C22.2 no. 42 (for cold conditions) pin-temperature 70 °C, 10 A, Protection Class I
Fuseholder	1-/2-pole, Shocksafe category PC2 acc. to IEC 60127-6, for fuse-links 5 x 20 / 6.3 x 32 mm
Rated Power Acceptance @ Ta 23 °C	5 x 20: 2.5W (1 pole)/ 2W (2-pole) per pole 6.3 x 32: 3.15W (1 pole)/ 2.5W (2-pole) per pole
Power Acceptance @ Ta > 23°C	Admissible power acceptance at higher ambient temperature see derating curves
Voltage Selector	optional, step, 3 pos.
Line Filter	Standard and Medical Version, IEC 60939, UL 1283, CSA C22.2 no. 8 Technical Details
MTBF	> 1'700'000h acc. to MIL-HB-217 F

Approvals and Compliances

Detailed information on product approvals, code requirements, usage instructions and detailed test conditions can be looked up in Details about Approvals

SCHURTER products are designed for use in industrial environments. They have approvals from independent testing bodies according to national and international standards. Products with specific characteristics and requirements such as required in the automotive sector according to IATF 16949, medical technology according to ISO 13485 or in the aerospace industry can be offered exclusively with customer-specific, individual agreements by SCHURTER.

Approvals

The approval mark is used by the testing authorities to certify compliance with the safety requirements placed on electronic products. Approval Reference Type: KFC

Approval Logo	Certificates	Certification Body	Description
10	VDE Approvals	VDE	Certificate Number: 40004665 (FKO, FKP, FKQ, FKR)
c FU °us	UL Approvals	UL	UR File Number: E72928 (FKO, FKP, FKQ, FKR)
Cac	CQC Approvals	CQC	CQC Certificate Number: CQC19001212148

Product standards

Product standards that are referenced

Organization	Design	Standard	Description
<u>IEC</u>	Designed according to	IEC 60320-1	Appliance couplers for household and similar general purposes
<u>IEC</u>	Designed according to	IEC 60939	Passive filters for suppressing electromagnetic interference
<u>IEC</u>	Designed according to	IEC 60127-6	Miniature fuses. Part 6. Fuse-holders for miniature fuse-links
<u>IEC</u>	Designed according to	IEC 61058-1	Switches for appliances. Part 1. General requirements
(ŲL)	Designed according to	UL 498	Standard for Attachment Plugs and Receptacles
(UL)	Designed according to	UL 1283	Passive filters for suppressing electromagnetic interference
CSA Group	Designed according to	CSA C22.2 no. 42	General Use Receptacles, Attachment Plugs, and Similar Wiring Devices
CSA Group	Designed according to	CSA C22.2 no. 8	Electromagnetic interference (EMI) filters

Application standards

Application standards where the product can be used

Organization	Design	Standard	Description
<u>IEC</u>	Suitable for applications acc.	IEC/UL 62368-1	Audio/video, information and communication technology equipment - Part 1: Safety requirements
IEC.	Suitable for applications acc.	IEC 60601-1	Medical electrical equipment - Part 1: General requirements for basic safety and essential performance
<u>IEC</u>	Suitable for applications acc.	IEC 60335-1	Safety of electrical appliances for household and similar purposes. Meets the requirements for appliances in unattended use. This includes the enhanced requirements of glow wire tests acc. to IEC 60695-2-11 or -12 & -13.


Compliances

The product complies with following Guide Lines

The product complies w	iti i lollowii ig dulde Lii les		
Identification	Details	Initiator	Description
C€	CE declaration of conformity	SCHURTER AG	The CE marking declares that the product complies with the applicable requirements laid down in the harmonisation of Community legislation on its affixing in accordance with EU Regulation 765/2008.
UK CA	UKCA declaration of conformity	SCHURTER AG	The UKCA marking declares that the product complies with the applicable requirements laid down in the British Amendment of Regulation (EC) 765/2008.
ROHS	RoHS	SCHURTER AG	Directive RoHS 2011/65/EU, Amendment (EU) 2015/863
©	China RoHS	SCHURTER AG	The law SJ / T 11363-2006 (China RoHS) has been in force since 1 March 2007. It is similar to the EU directive RoHS.
REACH	REACH	SCHURTER AG	On 1 June 2007, Regulation (EC) No 1907/2006 on the Registration, Evaluation, Authorization and Restriction of Chemicals 1 (abbreviated as "REACH") entered into force.
V -Lock		SCHURTER AG	V-Lock system are based on a matching plug-dose combination. The connector is equipped with a notch intended for use with the latching cordset. The cord latching system prevents against accidental removal of the cordset.
00	White Paper Glow wire test	SCHURTER AG	Meets the requirements of IEC 60335-1 for appliances in unattended use. This includes the enhanced requirements of glow wire tests acc. to IEC 60695-2-11 or -12 &-13.
T	Medical Equipment	SCHURTER AG	Suitable for use in medical equipment according to IEC/UL 60601-1 (1 MOOP, 1 MOPP)

Dimensions [mm]

KFC




Technical Data of Filter-Components


	•				
Rated Current [A]	Filter-Type	Inductances L [mH]	Capacitance CX [nF]	Capacitance CY [nF]	R [M Ω]
1	Standard version	2 x 10	68	2.2	-
2	Standard version	2 x 4	68	2.2	-
4	Standard version	2 x 1.5	68	2.2	-
6	Standard version	2 x 0.8	68	2.2	-
10	Standard version	2 x 0.3	68	2.2	-
1	Medical Version (M5)	2 x 10	68	-	1
2	Medical Version (M5)	2 x 4	68	-	1
4	Medical Version (M5)	2 x 1.5	68	-	1
6	Medical Version (M5)	2 x 0.8	68	-	1
10	Medical Version (M5)	2 x 0.3	68	-	1

Diagrams

Standard version with voltage selector

Medical Version (M5) with voltage selector







x) external connection to be made by the customer


- 1) Line
- 2) Load


- x) external connection to be made by the customer
- 1) Line
- 2) Load

Derating Curves










- - - - 50Ω differential mode _____ 50Ω common mode


Attenuation Loss

Standard version


1 A




2 A




4 A



6 A




10 A




Medical version (M5)


1 A




2 A




4 A



6 A



10 A



All Variants

Rated Current [A]	Filter-Type	Fuseholder	Voltage Selector	V-Lock	Order Number
1	Standard version	1-pole	-		4303.5011
2	Standard version	1-pole	-		4303.5012
4	Standard version	1-pole	-		4303.5013
6	Standard version	1-pole	-		4303.5014
10	Standard version	1-pole	-		4303.5015
1	Standard version	1-pole	3 pos.		4303.5031
2	Standard version	1-pole	3 pos.		4303.5032
4	Standard version	1-pole	3 pos.		4303.5033
6	Standard version	1-pole	3 pos.		4303.5034
10	Standard version	1-pole	3 pos.		4303.5035
1	Standard version	2-pole	-		4303.5001
2	Standard version	2-pole	-		4303.5002
4	Standard version	2-pole	-		4303.5003
6	Standard version	2-pole	-		4303.5004



Rated Current [A]	Filter-Type	Fuseholder	Voltage Selector	V-Lock	Order Number	
10	Standard version	2-pole	-		4303.5005	
1	Standard version	2-pole	3 pos.		4303.5021	
2	Standard version	2-pole	3 pos.		4303.5022	
4	Standard version	2-pole	3 pos.		4303.5023	
6	Standard version	2-pole	3 pos.		4303.5024	
10	Standard version	2-pole	3 pos.		4303.5025	
1	Medical Version (M5)	2-pole	3 pos.		4303.5221	
2	Medical Version (M5)	2-pole	3 pos.		4303.5223	
4	Medical Version (M5)	2-pole	3 pos.		4303.5225	
6	Medical Version (M5)	2-pole	3 pos.		4303.5227	
10	Medical Version (M5)	2-pole	3 pos.	•	4303.5209.21	
10	Medical Version (M5)	2-pole	3 pos.		4303.5229	

Most Popular.

Availability for all products can be searched real-time: https://www.schurter.com/en/info-center/support-tools/stock-checkdistributors

The fuse drawer is not included and must be ordered separately (see required accessory).

Packaging unit

10 Pcs

Required Accessory

Description

Fusedrawer_3



Fusedrawer for Fuse Links 5x20 mm resp. 6.3x32 mm

Fingergrip, 5 x 20, 2-pole, Voltage Selector 4303.20	
Fingergrip, 5 x 20, 2-pole, Voltage Selector, 100, 120, 220, 240 4303.20	14.01
Fingergrip, 5 x 20, 2-pole, Voltage Selector, 110, 150, 220 4303.20	14.02
Fingergrip, 5 x 20, 2-pole, Voltage Selector, 110, 220 4303.20	14.03

Accessories



Assorted_Covers Rear Cover

0859.0072



RC320 Rear Cover for Power Entry Module



Cord_retaining_kits Cord retaining strain relief

Flat head, A 4700.0001

Mating Outlets/Connectors

Category / Description

Appliance Outlet Overview complete



4787, Mounting: Screw-on mounting, Appliance Outlet: IEC Solder terminals, 10 A, Suitable for appliances with protection class I	4787
4788, Mounting: Snap-in version, Appliance Outlet: IEC Solder / Quick Connect, 10 A, Suitable for appliances with protection class I	4788
IEC Appliance Outlet F or H, Screw-on Mounting, Front Side, Solder, PCB or Quick-connect Terminal	5091

Connector Overview complete



4782 Mounting: Power Cord, 3 x 1 mm 2 / 3 x 18 AWG, Cable, Connector: IEC C13	4782
4785 Mounting: Power Cord, 3 x 1 mm ² / 3 x 18 AWG, Cable, Connector: IEC C13	4785
$4300\text{-}06$ Mounting: Power Cord, 3 x 1 mm^2 / 3 x 18 AWG, Cable, Connector: IEC C13	4300-06
4781 Mounting: Power Cord, Cable, Connector: IEC C15	4781
4784 Mounting: Power Cord, 3 x 1 mm ² / 3 x 18 AWG, Cable, Connector: IEC C15	4784

Mating Outlets/Connectors shuttered



Connector Overview complete



Power Cord Overview complete

VAC13KS, Overview, V-Lock cord retaining, diverse Connector IEC C13, diverse, bla	k VAC13KS